







The → mark shows the piping direction.




Wireless remote control

(ARC470A1)





Terminal block with earth terminal  
Located inside of the unit



Drain hose  
Inside diameter: 14 mm  
Outside diameter: 16 mm  
Connecting part

Liquid pipe  
Ø6.4 mm: CuT  
The length of the pipe outside the unit is 410 mm.

Gas pipe  
Ø9.5 mm: CuT  
The length of the pipe outside the unit is 360 mm.



Standard location of holes in the wall