


# FTXJ-AB9


# FTXJ-AS9

# FTXJ-AW9

### • Outside size






Connector (Model: B04B-PASK)  
(1pin:Vin 2pin:Ans 3pin:HL 4pin:GND)



### • Method of mounting

Don't blockage the vent of streamer unit.  
Ensure the exit wind speed 0.2m/sec of the vent.  
Ensure the spatial distance 8.5mm over at the vent of streamer unit.



### • Main specifications

Items		Contents	
Outside	Outside size	150.9×46.9×27.5mm	
	Weight	100g	
Material of resin	Material	ABS	
	Flame retardance	UL94-5VA	
	Tracking index	Over CTI600V	
Applicable laws		Electrical Appliance and Material Safety Act IEC60335-1(4th), IEC60335-2-65(4th)	
Ambient conditions	Storage temperature	-25~70 (Non-Energization)	
	Operating ambient temperature	-10~60 (Energization)	
	Operating ambient humidity	5~95%RH (No dew deposit)	
Basic specifications	Input voltage	14V±5%	
	Maximum output voltage	6.5±0.5kV	
	Rating output voltage	5.0±0.5kV	
	Rating output current	Hi	55.5μA±10%
		Lo	10μA±10%
	ON/OFF	Inputted voltage into Vin (ON/OFF)	
	Hi ↔ Lo Switching	Inputted 5V into HL (Loe tap)	
	Current monitor	Yes	
	Detectable over current	Yes	
Detectable low voltage	Under 3kV		
Generation amount of Ozone	4.26ml/hr (Hi 14±2; 50±10%RH)		
Method of mounting	Fixing by the right and left hook		
	Fixing by the screw section		